

# MicroMax® NS TRINE



Type 5 & 6 protective coverall with protective rear sleeve for harness lanyard.

- Allows harness and lanyard to be worn inside coverall.
- Protects harness and lanyard from damaging liquids, paints and chemicals - reduces costs.
- Lanyard sleeve folds away neatly in rear pouch when not in use.
- Velcro fastened lanyard sleeve for easy fitting.
- Tested at SATRA fall-arrest rig: garment remains intact when a fall incident occurs, maintaining protection for wearer. (See video – use QR code or URL below)
- High quality microporous film laminate fabric - soft, flexible and comfortable to wear.
- Coverall with elasticated hood, waist, wrists and ankles. Fold away lanyard sleeve to rear.
- Improved Super-B style coverall: superior fit, wearability and durability.
- Three-piece hood, inset sleeves and diamond crotch gusset results in best fitting garment on the market.

### Physical Properties

		MicroMax® NS /TS	MicroMax®	SafeGard® GP	SafeGard® 76	Flashspun PE
Property	EN Std	CE Class	CE Class	CE Class	CE Class	CE Class
Abrasion Resistance	EN 530	3	2	3	6	2
Flex Cracking	ISO 7854	6	6	6	6	6
Trapezoidal Tear	ISO 9073	3/2	4/2	3	3/2	1
Tensile Strength	EN 13934	2/1	2	3	2/1	1
Puncture Resistance	EN 863	1	1	1	1	2
Burst Strength	EN 13938	2	3	2	3	2
Seam Strength	EN 13935	3	3	3	3	3

### Chemical Repellency and Penetration EN 6530

Chemical	MicroMax® NS/TS		MicroMax®		SafeGard® GP		SafeGard® 76		Flashspun PE	
	R	P	R	P	R	P	R	P	R	P
Sulphuric Acid 30% CAS No. 67-64-1	3	3	3	3	3	3	3	3	3	3
Sodium Hydroxide CAS No. 1310-73-2	3	3	3	3	3	3	3	3	3	3
O-Xylene CAS No. 75-15-0	3	2	3	2	NT	NT	NT	NT	1	1
Butanol CAS No. 75-09-2	3	2	3	2	NT	NT	NT	NT	2	1

### Breathability - measured by air permeability and moisture vapour transmission rate (MVTR)


	MicroMax® NS/TS	MicroMax®	SafeGard® GP	SafeGard® 76	Flashspun PE	Cotton T-shirt
Air permeability cubic feet/minute (cfm)	<0.5	<0.5	40	40	~3.3	180
MVTR	119.3	NT	NT	NT	111.2	NT

### Infectious Agent / Biological Hazard Protection

Tested according to EN 14126. This consists of four different tests to assess protection against different forms of classification. Note these tests are on fabric only. We would always recommend a garment with sealed seams such as MicroMax® TS for protection against infectious agent hazards.

Test Description	Test No.	MicroMax® NS/TS	SafeGard® GP/76	Flashspun PE
Protection against blood and body fluids	ISO 16604:2004	6 (max is 6)	Not recommended	<1
Protection against biologically contaminated aerosols	ISO 22611:2003	3 (max is 3)	Not recommended	1
Protection against dry microbial contact	ISO 22612:2005	3 (max is 3)	Not recommended	1
Protection against mechanical contact with substances containing contaminated liquids	EN 14126:2003 Annex A	6 (max is 6)	Not recommended	1

## MicroMax® NS TRINE Style



Style Code: EMN428WH

Coverall with elasticated hood, waist, wrists and ankles. Rear sleeve for fall arrest harness lanyard.

Sizes: S - XXXL

Available in: White

MicroMAX® NS TRINE has been tested at the SATRA fall-arrest rig to ensure it stays intact in a fall incident. Use the QR link to watch the video.



[www.lakeland.com/europe/blog/cat/videos/post/mmnstrine/](http://www.lakeland.com/europe/blog/cat/videos/post/mmnstrine/)

Air permeability is a measure of the fabric's tendency to allow air to pass through and is the best indicator of comfort. The higher the breathability, the better the comfort for the wearer. The results show that fabrics such as Microporous films (MicroMax®) and flashspun polyethylene have very low and very similar levels of breathability; both are as close to zero as makes little practical difference. By contrast SMS fabric (SafeGard) has more than ten times the breathability and a standard cotton T-shirt has four times that of an SMS fabric.

Areas shaded green indicate where MicroMax® is equal to or better than the other fabric options.

## Super-B Style Design Features

Image shows MicroMax® NS Cool Suit >>>

### 1. Three-Piece Hood

The three-piece hood results in a 3D shape which is more rounded and fits the head better, moving freely with wearer movement and resulting in a more comfortable and durable garment as well as fitting a respirator mask rim more effectively.

### 2. Inset Sleeves

Inset sleeves result in greater freedom of movement and less stress on seams - especially at the crotch.

In addition there is less pulling back of sleeves during use, so Lakeland garments require no thumb loops - which can catch on machinery and be a hazard.

### 3. Diamond Crotch Gusset

The crotch features a diamond shaped 2-piece gusset which creates a better fitting shape allowing greater freedom of movement and taking stress away from the critical crotch area.



### 4. Chest Label

Lakeland chest labels feature all CE labelling requirements. So users and manager's can easily see wearers have the correctly certified garment.



This image compares the body/arm shape of a Lakeland Super-B style coverall (in red) with a typical 'batwing' sleeve competitor coverall.

The Lakeland coverall shape follows the body, improving freedom of movement and reducing stress on crotch and sleeves.



The Lakeland Super-B style coverall features a unique combination of:


- 1) Three-piece hood    2) Inset sleeves    3) Diamond crotch gusset

This results in one of the best fitting, most wearable, most comfortable garments available ... and no need for uncomfortable thumb-loops!

## Type 5 & 6 Seams

Lakeland's Type 5 & 6 coveralls feature either serged or stitched and bound seams.

See individual data sheets for details.



## Type 5 & 6 Suit Selection


Selection of an appropriate coverall is vital in optimising protection, comfort, durability and cost. Selection should be considered according to several factors.

<b>1.</b> Protection and fabric types	Is protection or breathability paramount? Which fabric is most suitable?
<b>2.</b> CE Testing - Physical properties and comparisons	Which physical properties are important to the environment or task? Select a garment that suits the task!
<b>3.</b> CE Testing - Effectiveness of liquid protection	Where liquid penetration protection is required; which fabrics offer superior liquid protection? Microporous film laminates (MicroMax®, MicroMax® NS) feature the best liquid protection of Type 5 & 6 garments available.
<b>4.</b> Comfort and breathability	Where comfort is paramount; which fabric type offers the superior breathability & comfort? SMS-type fabric (SafeGard® GP, SafeGard® 76) feature the highest breathability of Type 5 & 6 fabrics available.
<b>5.</b> Design Features	What design features might be important to the task and environment? Not all disposable coveralls are the same.

For more information request a copy of Lakeland's 'Guide to Type 5 & 6 Coverall Selection'

## Garment Sizing

Lakeland garments are cut and sized generously and according to the Super-B style for maximum freedom.



Size	Body Height (cm)	Chest (cm)	Waist (cm)
S	164-170	84-92	82-88
M	170-176	92-100	88-94
L	176-182	100-108	94-100
XL	182-188	108-116	100-106
XXL	189-194	116-124	106-112
XXXL	194-200	124-132	112-114

Selection of the appropriate sized garment is important in maximising comfort, protection and durability.

### Storage

Lakeland coveralls are supplied individually (unless specified) sealed, vacuum packed in polythene bags and outer cardboard cartons.

As materials are unaffected by normal conditions garments can be stored in standard warehousing facilities. In general keep dry and avoid very warm temperatures or temperatures below -10°C.

Avoid direct sunlight or other strong light for extended periods.

### Shelf-Life

With bags un-opened, properly stored in cool, dry conditions and away from sunlight or strong light, garments should achieve a shelf life of ten years or more. Some discolouration may occur over time, especially in garments left in sunlight and in particular white fabric may gain a slight yellow tinge, but this does not affect garment performance.

For suits designed to protect against hazardous chemicals we would

recommend that after a maximum of 10 years, suits are downgraded to 'training suits' or disposed of suitably.

Where anti-static properties are important however, anti-static treatments may erode in time and with wear.

Before use, all garments, regardless of age, should always be given a visual inspection for any damages or tears and to ensure any parts such as zips etc. function properly. Any garments that are damaged or worn in any way should not be used in any hazardous situation.

### Disposal

Uncontaminated garments can be disposed of via any standard method and according to local regulations. They be included with standard refuse into landfill or can be incinerated without any hazardous emissions - subject to local legal requirements.

However, garments contaminated with any chemicals must be disposed of appropriately with particular reference to the disposal requirements of the chemical and any local or national regulations. It is the users' responsibility to ensure contaminated garments are disposed of appropriately accordingly.

\* Competitor brand results are from competitors' own websites and were correct at the time of publication. Users are recommended to check up to date information with competitors before making any assessment based on specific chemicals. Other chemical test results may be available from competitors.